

Portavo 902 Cond

The basic version for mobile conductivity measurement.

Robust, intuitive portable analyzer for routine daily measurements in laboratories and processes.

Facts and Features

- Memosens sensors or analog sensors for conductivity measurement can be used on one device.
- A sensor quiver protects the sensor from drying out or being damaged in daily use.
- Robust housing with IP66/67, also for outdoor use
- The mineral glass display is perfectly readable even after years
- Temperature probe adjustment in the Memosens sensor (offset correction)





MEMO SENS

3-year warranty!

Specifications

Conductivity input, analog	Multi-contact for 2-/4-electrode sensors with integrated temp detector	
Measuring ranges	SE 202 sensor:	0.01 ... 200 $\mu\text{S}/\text{cm}$
	SE 204 sensor:	1 $\mu\text{S}/\text{cm}$... 500 mS/cm
	2-electrode sensors:	0.1 $\mu\text{S} \cdot \text{cm} \dots 200 \text{mS} \cdot \text{cm}^4$
	4-electrode sensors:	0.1 $\mu\text{S} \cdot \text{cm} \dots 1000 \text{mS} \cdot \text{cm}^4$
Permissible cell constant	0.005 ... 200.0 cm^{-1} (adjustable)	
Measurement error ^{1,2,3)}	< 0.5 % meas.val. + 0.4 $\mu\text{S} \cdot \text{cm}^4$	
Temperature input	2 x 4 mm dia. for integrated or separate temperature detector	
Measuring ranges	NTC 30 k Ω	-20 ... 120 $^{\circ}\text{C}$ / -4 ... 248 $^{\circ}\text{F}$
	Pt1000	-40 ... 250 $^{\circ}\text{C}$ / -40 ... 482 $^{\circ}\text{F}$
Measuring cycle	Approx. 1 s	
Measurement error ^{1,2,3)}	< 0.2 K ($T_{\text{amb}} = 23 \text{ }^{\circ}\text{C}$ / 73.4 $^{\circ}\text{F}$); TC < 25 ppm/K	
Conductivity input, Memosens	M8 socket, 4 pins, for Memosens lab cable	
Conductivity input	Measuring cycle	
	Approx. 1 s	
Temperature compensation	Linear 0 ... 20 %/K, reference temp. adjustable	
	nLF: 0 ... 120 $^{\circ}\text{C}$ / 32 ... 248 $^{\circ}\text{F}$	
	NaCl (ultrapure water with traces)	
	HCl (ultrapure water with traces)	
	NH3 (ultrapure water with traces)	
	NaOH (ultrapure water with traces)	
Display resolution (autoranging)	Conductivity ⁴⁾	0.001 $\mu\text{S}/\text{cm}$ ($c < 0.05 \text{ cm}^{-1}$)
		0.01 $\mu\text{S}/\text{cm}$ ($c = 0.05 \dots 0.2 \text{ cm}^{-1}$)
		0.1 $\mu\text{S}/\text{cm}$ ($c > 0.2 \text{ cm}^{-1}$)
	Resistivity	00.00 ... 99.99 $\text{M}\Omega \cdot \text{cm}$
	Salinity	0.0 ... 45.0 g/kg (0 ... 30 $^{\circ}\text{C}$ / 32 ... 86 $^{\circ}\text{F}$)
	TDS	0 ... 1999 mg/l (10 ... 40 $^{\circ}\text{C}$ / 50 ... 104 $^{\circ}\text{F}$)
	Concentration	0.00 ... 9.99 wt%
Concentration determination	NaCl	0.00 ... 9.99 wt% (0 ... 60 $^{\circ}\text{C}$ / 32 ... 140 $^{\circ}\text{F}$)
	HCl	0.00 ... 9.99 wt% (-20 ... 50 $^{\circ}\text{C}$ / -4 ... 122 $^{\circ}\text{F}$)
	NaOH	0.00 ... 9.99 wt% (0 ... 100 $^{\circ}\text{C}$ / 32 ... 212 $^{\circ}\text{F}$)
	H ₂ SO ₄	0.00 ... 9.99 wt% (-17 ... 110 $^{\circ}\text{C}$ / 1.4 ... 230 $^{\circ}\text{F}$)
	HNO ₃	0.00 ... 9.99 wt% (-17 ... 50 $^{\circ}\text{C}$ / 1.4 ... 122 $^{\circ}\text{F}$)
Sensor standardization	Cell constant	Input of cell constant with simultaneous display of conductivity value and temperature
	Input of solution	Input of conductivity of the calibration solution with simultaneous display of cell constant and temperature
	Auto	Automatic determination of the cell constant with KCl solution or NaCl solution
	Temperature calibration (TAN option)	Software option SW-P002 for temperature probe adjustment in the Memosens sensor (offset correction)
Connections	2 x socket, 4 mm dia., for separate temperature probe	
	1 x M8 socket, 4 pins, for Memosens lab cable	
	1 x multi-contact socket for 2- and 4-electrode sensors	

Specifications

Display	LCD STN 7-segment display with 3 lines and icons Sensoface Provides information on the sensor condition Status indicators for battery power level Notices Hourglass
Keypad	[on/off], [cal], [meas], [set], [▲], [▼], [clock]
Diagnostic functions	Sensor data (Memosens only) Manufacturer, sensor type, serial number, operating time Calibration data Calibration date; cell constant Device self-test Automatic memory test (FLASH, EEPROM, RAM) Device data Device type, software version, hardware version
Data retention	Parameters, calibration data > 10 years
EMC	EN 61326-1 (General Requirements) Emitted interference Class B (residential environment) Immunity to interference Industrial applications EN 61326-2-3
RoHS conformity	According to directive 2011/65/EU
Power supply	4 x AA alkaline or lithium batteries Operating time Approx. 1000 h (alkaline)
Nominal operating conditions	Ambient temperature -10 ... 55 °C / 14 ... 131 °F Transport/Storage temp. -25 ... 70 °C / -13 ... 158 °F Relative humidity 0 ... 95 %, short-term condensing allowed
Housing	Material PA12 GF30 (silver gray RAL 7001) + TPE (black) Protection IP 66/67 with pressure compensation Dimensions Approx. 132 x 156 x 30 mm / 5.2 x 6.14 x 1.18 inches Weight Approx. 500 g / 1.10 lbs

* user-defined

1) at nominal operating conditions

2) ± 1 count

3) plus sensor error

4) c = cell constant

По вопросам продаж и поддержки обращайтесь:

Архангельск (8182)63-90-72
Астана +7(7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395) 279-98-46
Киргизия (996)312-96-26-47

Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Казахстан (772)734-952-31

Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Таджикистан (992)427-82-92-69

Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93